

Product Information

VESTAKEEP® DC 4400 G GN**GREEN POLYETHER ETHER KETONE FOR DENTAL APPLICATIONS**

VESTAKEEP® DC4400 G GN is a green, high viscosity polyether ether ketone (PEEK) resin.

Biocompatibility of VESTAKEEP® Dental

For VESTAKEEP® DC4400 G GN, biocompatibility is designed for permanent mucous membrane contact. The compound composition is optimised for high biocompatibility and superior mechanical, thermal and chemical resistance.

Processing of VESTAKEEP® Dental

VESTAKEEP® DC4400 G GN can be processed by common melt processing techniques like injection molding and extrusion.

For injection molding, we recommend a melt temperature in the 380°C to 400°C range. The mold temperature should be within 160°C to 200°C, preferably 180°C.

Delivery of VESTAKEEP® Dental

VESTAKEEP® DC4400 G GN is supplied as granules in 5 and 25 kg boxes with moisture-proof polyethylene liners.

The values presented are typical or average values, they do not constitute a specification.

FOR FURTHER INFORMATION PLEASE CONTACT US AT EVONIK-HP@EVONIK.COM
OR VISIT OUR PRODUCT AT WWW.EVONIK.COM/MEDICAL-TECHNOLOGY

Key Features**Industrial Sector**

Medical Devices

Optics

Opaque

Processing

Injection molding, Extrusion

Conformity

Biocompatibility, Medical application

Delivery form

Pellets, Granules

Mechanical properties ISO

Tensile modulus

dry

3500

Unit

MPa

Test Standard

ISO 527

Tensile strength

95

MPa

ISO 527

Yield stress

95

MPa

ISO 527

Yield strain

5

%

ISO 527

Nominal strain at break, tB	20	%	ISO 527
Charpy impact strength, +23°C	N	kJ/m ²	ISO 179/1eU
Charpy impact strength, -30°C	N	kJ/m ²	ISO 179/1eU
Charpy notched impact strength, +23°C	7	kJ/m ²	ISO 179/1eA
Type of failure	C	-	-

Thermal properties	dry	Unit	Test Standard
Melting temperature	340	°C	ISO 11357-1/-3
Vicat softening temperature A, 10 N, 50 K/h	335	°C	ISO 306
Vicat softening temperature B, 50 N, 50 K/h	305	°C	ISO 306
Coeff. of linear therm. expansion, 23°C to 55 °C, parallel	45	E-6/K	ISO 11359-1/-2

Physical properties	dry	Unit	Test Standard
Density	1300	kg/m ³	ISO 1183

Rheological properties	dry	Unit	Test Standard
Melt volume-flow rate, MVR	10	cm ³ /10min	ISO 1133
Temperature	380	°C	-
Load	5	kg	-
Molding shrinkage, parallel	0.9	%	ISO 294-4, 2577
Molding shrinkage, normal	1.0	%	ISO 294-4, 2577

Polymer analytics	dry	Unit	Test Standard
Ash content	21.2	%	ISO 3451

Test specimen production	dry	Unit	Test Standard
Injection Molding, melt temperature	380	°C	ISO 294
Injection Molding, mold temperature	180	°C	ISO 294

Characteristics

Applications

Dental applications

Special Characteristics

Semi-crystalline, High viscosity

Regulatory

Cytotoxicity ISO 10993-5

Color

Green

Chemical Resistance

Acid resistance, Alkali resistance, Solvent resistance, Grease resistance, Hydrolytically stable, Oxidation resistance, General chemical resistance

This information and all technical and other advice are based on Evonik's present knowledge and experience. However, Evonik assumes no liability for such information or advice, including the extent to which such information or advice may relate to third party intellectual property rights. Evonik reserves the right to make any changes to information or advice at any time, without prior or subsequent notice. Evonik disclaims all representations and warranties, whether express or implied, and shall have no liability for, merchantability of the product or its fitness for a particular purpose (even if Evonik is aware of such purpose), or otherwise. EVONIK SHALL NOT BE RESPONSIBLE FOR CONSEQUENTIAL, INDIRECT OR INCIDENTAL DAMAGES (INCLUDING LOSS OF PROFITS) OF ANY KIND. It is the customer's sole responsibility to arrange for inspection and testing of all products by qualified experts. Reference to trade names used by other companies is neither a recommendation nor an endorsement of the corresponding product, and does not imply that similar products could not be used.

* is a registered trademark of Evonik Industries AG or one of its subsidiaries

Evonik Operations GmbH
Smart Materials
High Performance Polymers
 45772 Marl / Germany
 Tel: +49 2365 49-9878
evonik-hp@evonik.com
www.plastics-database.com